



GOLDENROD 495 FUEL TANK FILTER

- 10 micron particle only fuel filter to remove dust, rust and other contaminants
- Clear bowl containing paper cartridge and drain port to easily remove filtered impurities
- For use in both gravity systems and pump installations, therefore widely recognised within the agricultural market
- > Maximum flow rate of 95lpm
- > 1" F BSP Inlet/Outlet
- > 1 1/8"-12M UNF filter thread
- > Heavy duty zinc die-cast head with excellent seal
- > Suitable for diesel, bio up to B20 and petrol
- > Complete filter contains one element, one head, bowl and gasket





Filter Element

Complete Filter

Installation

Attach filter top cap to storage tank valve on opening marked "IN". Be sure there is a shutoff valve between filter and tank. Attach hose and nozzle to filter opening marked "OUT".


! Don't tighten filter cap using the filter bowl for leverage. Apply wrench to flat surfaces in center of filter cap to tighten or remove !

When installing the element and bowl, apply a coating of oil to each side of gasket #202204. These components should be hand tightened only. Over tightening of the filter bowl will result in difficulty in removal at a later date. When assembly is complete, check for leaks. Change filter element when dirty or when flow is restricted.

Tip: We'd recommend using the wrench for removal of the element, as this will stop the bowl from cracking when replacing it.

CAUTION!

This filter is rated for 150 psi pressure. If the fuel system is prone to violent pressure surges (water hammers, etc.), a pressure cushion device should be installed. A vertical capped pipe installed in the line near the filter so that it traps a pocket of air will serve this function. Only if surges above 150 psi occur.



| Code | GoldenRod Part No. | Description | Micron | Max Flow | Max Bar | Inlet/Outlet | Fluids |
|---------|--------------------|---|--------|----------|---------|--------------|--------|
| CTJ1800 | 495 | GoldenRod Particle Only Complete Filter | 10µ | 95 lpm | 10 | 1" F BSP | D B2 P |
| CTJ1801 | 470-5 | GoldenRod Replacement Element | 10µ | 95 lpm | 10 | 1" F BSP | D B2 P |
| CTJ1802 | 495-4 | GoldenRod Replacement Bowl | | | | | |
| CTJ1818 | 470-1 | GoldenRod Replacement Head | | | | 1" F BSP | |
| CTJ1813 | 491 | Filter Wrench | | | | | |



Unit H1, Adanac North, Adanac Drive, Southampton SO16 0BT
sales@commercialfuelsolutions.co.uk \$\\$ +44(0)2380 118670
www.commercialfuelsolutions.co.uk